

SGE[®] GC COLUMNS

forte™ BPX70

Alternative to:

| | |
|-----------|----------|
| DB-23 | Rtx-2330 |
| SP-2330 | SP-2380 |
| CP-Sil 88 | |

Applications

| |
|--|
| Fatty acid methyl esters (FAMES) CIS/TRANS |
| Carbohydrates |
| Pharmaceuticals |

Operating Temperatures

| | |
|---------------------|------------------------|
| Film df(μm): | Temp Limit: |
| 0.25, 0.50 | 50 °C to 250 °C/260 °C |


ORDERING INFORMATION

| BPX70 | | | | |
|-----------------|--------|----------|----------|-------|
| ID(mm) | df(μm) | Part No. | Mfr. No. | Price |
| 25-Meter | | | | |
| 0.22 | 0.25 | CGO-5507 | 054602 | |
| 0.32 | 0.25 | CGO-5516 | 054606 | |
| 0.53 | 0.50 | CGO-5522 | 054610 | |
| 30-Meter | | | | |
| 0.22 | 0.25 | CGO-5508 | 054612 | |
| 0.25 | 0.25 | CGO-5512 | 054622 | |
| 0.32 | 0.25 | CGO-5517 | 054616 | |
| 0.53 | 0.50 | CGO-5523 | 054620 | |
| 50-Meter | | | | |
| 0.22 | 0.25 | CGO-5509 | 054603 | |
| 0.32 | 0.25 | CGO-5518 | 054607 | |
| 60-Meter | | | | |
| 0.25 | 0.25 | CGO-5513 | 054623 | |
| 0.32 | 0.25 | CGO-5519 | 054617 | |

forte™ HT8

Applications

| |
|-----------------------------------|
| PCB Analyses |
| Nitro-substituted Aromatics |
| Polynuclear Aromatic Hydrocarbons |
| Pesticides/herbicides |



Operating Temperatures

| | |
|---------------------|-------------------------|
| Film df(μm): | Temp Limit: |
| 0.25, 0.5 | -20 °C to 360 °C/370 °C |

ORDERING INFORMATION

| HT8 | | | | |
|-----------------|--------|----------|----------|-------|
| ID(mm) | df(μm) | Part No. | Mfr. No. | Price |
| 12-Meter | | | | |
| 0.32 | 0.25 | CGO-5555 | 054679 | |
| 25-Meter | | | | |
| 0.22 | 0.25 | CGO-5553 | 054675 | |
| 0.32 | 0.25 | CGO-5556 | 054680 | |
| 0.53 | 0.50 | CGO-5558 | 054685 | |

forte™ BPX90

Applications

| |
|---------------|
| Fragrances |
| Aromatics |
| Petrochemical |
| PCBs |
| FAMES |

Operating Temperatures

| | |
|---------------------|--------------------|
| Film df(μm): | Temp Limit: |
| 0.25 - 0.50 | 80 °C to 280 °C |

ORDERING INFORMATION

| BPX90 | | | | |
|-----------------|--------|----------|----------|-------|
| ID(mm) | df(μm) | Part No. | Mfr. No. | Price |
| 30-Meter | | | | |
| 0.25 | 0.25 | CGO-8229 | 054580 | |
| 0.32 | 0.50 | CGO-8230 | 054583 | |

forte™ SolGel-WAX

Applications

| |
|-----------|
| Alcohols |
| Ketones |
| Aldehydes |

Operating Temperatures

| | |
|---------------------|--------------------|
| Film df(μm): | Temp Limit: |
| 0.25 - 1.00 | 30 °C to 300 °C |

ORDERING INFORMATION

| SolGel-WAX | | | | |
|-----------------|--------|----------|----------|-------|
| ID(mm) | df(μm) | Part No. | Mfr. No. | Price |
| 30-Meter | | | | |
| 0.25 | 0.25 | CGO-8234 | 054796 | |
| 0.32 | 0.50 | CGO-8235 | 054797 | |
| 0.53 | 1.00 | CGO-8236 | 054785 | |

forte™ BPX-VOLATILES

Applications

| |
|-----------------------------|
| EPA Method 624, 502.2, 8260 |
|-----------------------------|

Operating Temperatures

| | |
|---------------------|-----------------------|
| Film df(μm): | Temp Limit: |
| 1.0 - 3.0 | 0 °C to 290 °C/300 °C |

ORDERING INFORMATION

| BPX-Volatiles | | | | |
|-----------------|--------|----------|----------|-------|
| ID(mm) | df(μm) | Part No. | Mfr. No. | Price |
| 30-Meter | | | | |
| 0.25 | 1.40 | CGO-8231 | 054980 | |
| 0.32 | 1.80 | CGO-8232 | 054982 | |
| 0.53 | 3.00 | CGO-8233 | 054984 | |



All other SGE GC columns not listed are available.